



Reliable Connections

NEW



PEXGrip® Series Pinch Clamp Features:

- Patented PEXGrip® Technology.
- Preset to grip tube.
- Prevents clamp from sliding for easier crimping.
- Provides a 360 leak-free seal.
- Narrow band for concentrated seal compression.
- Requires only one installation tool for all clamp sizes.
- Tamper-evident design.
- Stepless® Ear Clamps 167 for PEX.
- ASTM F2098 for use with ASTM F1807 and F2159 insert fittings, ASTM F876 PEX tubing and ASTM F877 PEX systems.




Standard PEX clamp vs. PEXGrip® Clamp




Installation:

For proper Installation of clamps, use calibrated, genuine Oetiker installation tools.



1. Slip clamp over tubing. The recommended distance (dimension) between the clamp and end of the tube is 1/8" - 1/4"



2. Close clamp ear with tool. Tool will not release until clamp is fully closed.



3. IMPORTANT: For proper installation of Oetiker PEX clamps, full ear closure is required. Visually inspect clamp for correct closed ear form.

**STANDARD AGI DISCOUNTS DO NOT APPLY.
Contact your sales representative for pricing.**

**CB SUBCAT CODE #782
Crimp Rings**

Part Number	Description	PEX Tube	Bag/Case Qty	List Price
OETIKER PEXGrip® STAINLESS STEEL PINCH CLAMPS				
CBXSSPG2	PEXGrip SS Pinch Clamps	3/8"	100/2000	\$ 0.77
CBXSSPG3	PEXGrip SS Pinch Clamps	1/2"	100/2000	1.00
CBXSSPG58	PEXGrip SS Pinch Clamps	5/8"	50/2500	1.59
CBXSSPG4	PEXGrip SS Pinch Clamps	3/4"	50/2000	1.24
CBXSSPG5	PEXGrip SS Pinch Clamps	1"	50/1000	1.71

NEW